

技术资料

5013-1L | 硅油，类型 200.20，1 升（可用范围：10



产品概述: 5013-1L | 硅油，类型 200.20，1 升（可用范围：10

Silicone oil is used as a calibration media in temperature controlled baths. Different types of silicone oil are chosen for specific temperature ranges based on their viscosity at those temperatures. They have good thermal characteristics and low flammability.

- Silicone oil bath fluid type 200.20
- Usable range: 10 °C to 230 °C

- FlashPoint: 232 °C

Atmospheric pressure affects the usable range of some fluids. The temperatures quoted are at sea level.

Flash point is the temperature at which a vapor (not the fluid) will ignite if exposed to an open flame. When the flame is removed, the vapor will stop burning. (Open cup method).

型号



5013-3.8L

硅油，类型 200.20，1升（可用范围：10



Fluke. 让您的工作畅通无阻。

福禄克测试仪器（上海）有限公司 电话：400-810-3435 ©2025 福禄克公司
04/2025

北京福禄克世禄仪器维修和服务有限公司 电
话：400-615-1563 未经许可，本文档禁止修改
福禄克测试仪器（上海）有限公司上海维修中心 电
话：021-54402301, 021-54401908分机269
福禄克测试仪器（上海）有限公司深圳第一特约维修点
电话：0755-86337229